

If you're going to take time

TO POLISH
do it right

New Americal Plus


any system, any lens

- ✓ Exceptional surface quality on all lens types
- ✓ Ideal for AR and hard coatings
- ✓ Long life even in aggressive polycarbonate designated systems

No freeze issues! Unlike other polishes,
New Americal Plus can be thawed,
mixed and used after freezing.



1789 Transelco Drive, Penn Yan, New York 14527-9752 • Phone: 315/536-3357 www.ferro.com



11617 Prospect Road • Odessa, FL 33556 • Phone: 800/237-8154 • Fax: 800/330-3800

New & Improved Americal Plus

Available At PSI



Features & Benefits

- Performs equally on all lens materials (plastic, polycarbonate, high and mid-index materials).
- Manufactured under tight particle size distribution controls to ensure consistently high cut rates while maintaining a brilliant surface.
- Superior suspension system that will not hard settle or cake on equipment.
- Increased viscosity for pouring ease and to retard splashing without affecting product flowability.
- NO FREEZE ISSUES - maintains performance even after being frozen and thawed.
- Ideal for AR and hard coated lenses.
- Formulated to work in both large central slurry systems and single bowl applications.
- Non-foaming

Specifications

PSI Order #:	3320G - Gallon 3320P - 5-Gallon Pail
Baume:	25°
pH:	3.0 - 4.2
Particle Size (Coulter):	D50 - 1.83i
Stock Removal Rating:	97mg/6 minutes
Surface Quality Rating:	8.5

Recommended Usage

Polish Cycle:	6 to 7 minutes
Pin Pressure:	16 to 18 pounds or .4 bars
Speed:	High
Temperature:	Maintain at 55° to 65° F



Practical Systems, Inc.

11617 Prospect Road • Odessa FL 33556
(800) 237-8154 • Fax (800) 330-3800
(727) 376-7900 • Fax (727) 372-1900



LOOK TO PSI

Performance • Service • Integrity